


Nordstrand 2-Band Tone test



Sweep	Trace	Color	Line Style	Thick	Data	Axis	Comment
1	1	Red	Solid	3	Anlr.Ampl	Left	Tone : All Center
2	1	Blue	Solid	3	Anlr.Ampl	Left	Bass : Maximum, Dip switch : Open
3	1	Blue	Solid	3	Anlr.Ampl	Left	Bass : Minimum, Dip switch : Open
4	1	Green	Solid	3	Anlr.Ampl	Left	Treble : Maximum, Dip switch : Open
5	1	Green	Solid	3	Anlr.Ampl	Left	Treble : Minimum, Dip switch : Open
6	1	Black	Solid	3	Anlr.Ampl	Left	Treble : Maximum, Dip switch : Close
7	1	Black	Solid	3	Anlr.Ampl	Left	Treble : Minimum, Dip switch : Close